


Verticasa Breakout Unit – 4 Port

Prysmian Part Numbers: *See table below*



The Verticasa Breakout Unit – 4 Port is typically used in multi dwelling units to breakout and distribute the fibres from an in-line Verticasa cable into drop tubes, for routing to a customer premise. It has the capacity to accommodate Verticasa cables of up to 15mm in diameter. It enables a window to be cut in the cable to access the fibres, which can be spurred of into drop tubes of 4 or 5mm in diameter. Up to 4 drop tubes can be accommodated.

Features and Benefits

- Compact, low profile, wall mounted unit typically used in multi dwelling units.
- Unit manufactured from fire resistant material to UL94-V0.
- Supplied with all of the components required to mount the unit to a wall and secure an in-line Verticasa cable.
- Can accommodate Verticasa cables of up to 15mm in diameter.
- Can take out 4 drop tubes.
- Can be supplied to accommodate drop tubes of 4 or 5mm in diameter. See part numbers opposite.
- Standard colour is white RAL9016. Other colours are available on request. Please contact the Prysmian sales desk.

Kit Contents

- Wall fixings
- Cable Ties

Part Numbers

Verticasa Breakout Unit: -

- XCPSC00521 – 4mm drop tubes
- XCPSC00522 – 5mm drop tubes

Technical Data

- Max number of input cables: 1 in-line
- Max diameter of in-line cable (mm): 15
- Max number of drop cables: 4
- Max diameter of drop cables (mm): 5
- Required space envelope (mm): (h) 120 x (w) 50 x (d) 23
- Operating temperature: -20°C to + 60°C (5 to 95% RH)
- Material: FR ABS
- Colour: White RAL 9016
- Flammability rating: UL94-V0

Logistics

- Packing Dimensions (mm): (h) 130 x (w) 130 x (d) 30
- Packed Weight (kg): 0.045
- Net weight (kg): 0.035

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2008. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.